

Data Sheet

980nm Pump Laser Module - Grating Stabilized, 300mW LC94


These lasers are designed as pump sources for Erbium-Doped Fiber Amplifier (EDFA) applications. Processes and techniques of coupling the fiber to the laser allow high output powers that are very stable with both time and temperature. The grating is located in the pigtail to stabilize the wavelength. Devices are available with kink free output powers to 300mW. The LC94 series pump module utilises a double Fiber Bragg Grating design for enhanced wavelength and power stability performance. This product has been designed to ensure superior wavelength locking over drive current, temperature and optical feedback changes.

Features:

- Double Fiber Bragg Grating wavelength stabilization
- High output power, up to 300mW kink free
- Single-mode fiber pigtail
- Internal thermoelectric heatpump and monitor photodiode
- Hermetically sealed 14-pin butterfly package
- Telcordia GR-468-CORE compliant
- Field proven high reliability
- RoHS compliant 

Applications:

- Low noise EDFAs
- Dense wavelength division multiplexing (DWDM) EDFAs
- CATV Applications



Data Sheet

Characteristics

Conditions unless otherwise stated:

Case temperature -20 to +75°C

Submount temperature 25°C

Monitor diode bias -5V

CW operation

Kink-free fiber-coupled output power:
(Wavelength = 974nm)

LC94ZC74-20R	100mW	LC94A74-20R	200mW
LC94ZD74-20R	110mW	LC94B74-20R	210mW
LC94ZE74-20R	120mW	LC94C74-20R	220mW
LC94ZF74-20R	130mW	LC94D74-20R	230mW
LC94ZG74-20R	140mW	LC94E74-20R	240mW
LC94ZH74-20R	150mW	LC94F74-20R	250mW
LC94ZJ74-20R	160mW	LC94G74-20R	260mW
LC94ZK74-20R	170mW	LC94H74-20R	270mW
LC94ZL74-20R	180mW	LC94J74-20R	280mW
LC94ZM74-20R	190mW	LC94K74-20R	290mW
		LC94L74-20R	300mW


Parameter	Min	Typ	Max	Unit
Threshold current (I_{th})		30	40	mA
Operating drive current (I_f)				
ZC thru ZD			250	mA
ZE thru ZF			300	mA
ZG thru ZJ			350	mA
ZK thru ZM			400	mA
A thru B			450	mA
C thru E			500	mA
F thru K			550	mA
L			600	mA
Forward voltage (V_f)		1.9	2.5	V
Centre wavelength (λ_c)		974		nm
Spectral width (RMS @ -13dB)		0.2	1	nm
Spectrum stability (t = 60s)			±0.5	nm
Temperature dependence of peak wavelength			0.02	nm/°C
Wavelength tolerance			±0.5	nm
Monitor detector responsivity	1.0	8	25	μA/mW
Monitor dark current			50	nA
Thermistor resistance (at 25°C)	9.5	10	10.5	kΩ
Intended laser submount operating temperature	20	25	30	°C
Power stability Peak-to peak, t = 60s, DC to 50kHz sampling, $T_C = 25^\circ\text{C}$ >20mW 10-20mW			0.05 0.1	dB dB
Laser temperature, R = 10kΩ	23.5		26.5	°C
Heatpump current ($\Delta T = 50^\circ\text{C}$, $I_f = 500\text{mA}$)			1.3	A
Heatpump voltage ($\Delta T = 50^\circ\text{C}$, $I_f = 500\text{mA}$)			2.8	V

Data Sheet

Absolute Maximum Ratings

Parameter	Min	Max	Unit
Operating temperature	-20	75	°C
Storage temperature	-40	85	°C
Laser forward current		800	mA
Laser reverse voltage		2	V
Heatpump current		1.8	A
Lead soldering temperature (10s max)		260	°C
Fibre bend radius	30		mm


Package Outline Drawing and Dimensions



Data Sheet

Connections

Pin #	Description	Pin #	Description
1	Peltier cooler (+)	8	Not connected
2	Thermistor	9	Not connected
3	Monitor anode (-)	10	Laser anode (+)
4	Monitor cathode (+)	11	Laser cathode (-)
5	Thermistor	12	Not connected
6	Not connected	13	Case ground
7	Not connected	14	Peltier cooler (-)



Data Sheet

RoHS Compliance



Bookham is fully committed to environment protection and sustainable development and has set in place a comprehensive program for removing polluting and hazardous substances from all of its products. The relevant evidence of RoHS compliance is held as part of our controlled documentation for each of our compliant products. RoHS compliance parts are available to order, please refer to the ordering information section for further details.

Ordering Information:

LC94ZC74-20R for 100mW device
 LC94ZD74-20R for 110mW device
 LC94ZE74-20R for 120mW device
 LC94ZF74-20R for 130mW device
 LC94ZG74-20R for 140mW device
 LC94ZH74-20R for 150mW device
 LC94ZJ74-20R for 160mW device
 LC94ZK74-20R for 170mW device
 LC94ZL74-20R for 180mW device
 LC94ZM74-20R for 190mW device

LC94A74-20R for 200mW device
 LC94B74-20R for 210mW device
 LC94C74-20R for 220mW device
 LC94D74-20R for 230mW device
 LC94E74-20R for 240mW device
 LC94F74-20R for 250mW device
 LC94G74-20R for 260mW device
 LC94H74-20R for 270mW device
 LC94J74-20R for 280mW device
 LC94K74-20R for 290mW device
 LC94L74-20R for 300mW device

Contact Information

North America Bookham Worldwide Headquarters

2584 Junction Ave.
 San Jose
 CA 95134
 USA

- Tel: +1 408 919 1500
- Fax: +1 408 919 6083

www.bookham.com
sales@bookham.com

Europe Paignton Office

Brixham Road
 Paignton
 Devon
 TQ4 7BE
 United Kingdom

- Tel: +44 (0) 1803 66 2000
- Fax: +44 (0) 1803 66 2801

Asia Shenzhen Office

2 Phoenix Road
 Futian Free Trade Zone
 Shenzhen 518038
 China

- Tel: +86 755 33305888
- Fax: +86 755 33305805
 +86 755 33305807

Important Notice

Performance figures, data and any illustrative material provided in this data sheet are typical and must be specifically confirmed in writing by Bookham before they become applicable to any particular order or contract. In accordance with the Bookham policy of continuous improvement specifications may change without notice. The publication of information in this data sheet does not imply freedom from patent or other protective rights of Bookham or others. Further details are available from any Bookham sales representative.

